

EIT2.0[™] LLC On-Line Measurement **PRODUCT OVERVIEW**

BROADBAND & LED

ON-LINE MONITORING SYSTEMS

EIT's On-Line Systems measure UV intensity to provide continuous, real-time, feedback on a system. The solution is electro-optic based and can be used to monitor the UV from LED or Broadband (mercury) sources in situations where:

- Space is limited and a radiometer will not fit
- Arms, rollers and/or blades are present
- Sources are enclosed, not easily accessed or high off the ground
- Multiple sources are used to increase production line width
- Fast production speeds make it hard to use a radiometer
- UV conditions change rapidly due to off-gassing and/or contamination
- High value products are manufactured and undetected changes in the UV can lead to high scrap levels
- Continuous validation of the UV conditions is required
- The process window is tight

Applications include web presses, fiber optic draw towers, hard drive manufacturing, print and medical applications. The intensity measured by the On-Line Monitoring System is a relative intensity versus an absolute (W/cm²) value. The user is able to track both gradual (e.g. source aging) or sudden (equipment malfunction) changes to the UV intensity to take action before the changes impact product quality and bottom line profitability.

The On-Line System consists of two components: Compact Sensor and DIN Rail Signal-Conditioning Unit. The system can be used as the sole means of UV process control or in conjunction with an EIT NIST-traceable UV radiometer.




UV Intensity Monitor



Top: EIT Compact Sensor Center: EIT DIN Rail **Bottom: EIT Compact Sensor**

EIT Compact Sensor: An extremely durable sensor with sealed optics designed to withstand harsh UV environments. Sensors are available for LED or Broadband based sources. EIT and our representative/ distributor network will assist in selecting the optic response, housing shape, aperture size and mounting location based on the UV source type and application.





An EIT Compact Sensor mounted behind a UV reflector can provide continuous information on the lamp condition.



EIT DIN Rail units installed in cabinet to support multiple Compact Sensors used in production.


e-mail : info@es-canada.com \bowtie Site Web : www.es-canada.com

EIT COMPACT SENSOR DURABILITY


The Compact Sensor uses an innovative optics design to increase durability and reduce solarization (degradation of optical components) caused by intense UV energy. An EIT UVA Compact Sensor was tested for over 6,700 hours in an intense high power microwave UV system. The optics were characterized before and after the test. Results showed a very small decrease (4%) in the optical transmission characteristics.

The EIT Compact Sensor also has over twenty years of real world monitoring experience, making it the choice to monitor even the most intense UV sources without perceptible solarization.

SENSOR INSTALLATION LOCATIONS



The before and after scans of Compact Sensor optics after 6,700 hours of exposure to a high intensity microwave system



Selecting a location to install your Compact Sensor depends on your application and source. The Compact Sensor needs to remain clean and cool (< 100° C for UVA, UVB & UVV and < 70° C for UVC and LED Compact Sensors).


Installing the Compact Sensor where it 'sees' reflected energy is preferred to a location where it only 'sees' direct energy. Consider using the EIT Quartz Rod if physical access or high temperatures are a concern.

Suggested Sensor Installation Locations:

- 1. Behind the Reflector from top
- 2. Behind the reflector from side
- 3. Below the reflector looking up
- 4. Under system and/or quartz plate
- 5. End of lamp housing
- 6. Use of quartz rod or other material

COMPACT SENSOR INTERNAL APERTURE SIZE

The Compact Sensor internal aperture size is specified at the time of order and is determined by the type/power of the source, mounting location, angle of view to the source, housing type and whether or not an EIT Quartz Rod is used. EIT and our rep & distributor team will work to determine the best Compact Sensor for your application. We suggest testing Compact Sensors prior to placing a large order to insure optimal Compact Sensor performance and longevity.



Myriad Electronic Solutions Inc. d.b.a. ES Canada 422 Richard St, Vancouver, BC V6B 2Z4 Site Web : www.es-canada.com

ELECTRO MAGNETIC INTERFERENCE (EMI)

UV equipment (e.g., high-frequency power supply, power supply mounted in with the UV source, microwave source) has the potential to generate Electro Magnetic Interference (EMI) or electrical noise. A Compact Sensor cable, even with its shield, can also pick up electrical noise if it is run alongside a high voltage line. This electrical noise can make it appear that either the sensor and/or the source is unstable. The EMI Compact Sensor and EMI DIN Rail have been 'hardened' with additional circuitry to make them less susceptible to electrical noise or interference.

EMI COMPACT SENSOR & EMI DIN RAIL

The EMI Compact Sensor is identified by the "gold" circle on the electronics. The EMI Compact Sensor must be grounded <u>and</u> connected to an EMI DIN Rail with a three wire EMI cable for it to work. *Note: If the EMI Compact Sensor is used with the Standard DIN Rail and/ or two wire cable, there is no added EMI protection.* EMI Compact Sensors are currently available in UVA, UVB, UVC and UVV versions. In addition to the CS-1 and CS-2 housings, the EMI Compact Sensor is also available in a "BTR" (Behind The Reflector) housing which mounts behind the reflector of a lamp.




Left to Right: EMI Compact Sensor with "gold" circle; EMI Sensor with 3 wire cable; EMI DIN Rail; EMI Housings (BTR , CS-1, CS-2)



Feature	CS-1 With purge	CS-2 Without Purge	BTR (Behind the Reflector)	Standard DIN Rail DRM-007	EMI DIN Rail DRM-006
Size	0.57 x 1.10 x 0.75" (1.45 x 2.78 x 1.91 cm)	0.57 x 0.60 x 0.75" (1.45 x 1.52 x 1.91 cm)	0.55 x 0.55 x 1.55" (1.40 x 1.40 x 3.90 cm)	3.56 x 3.11 x 0.98" (9.04 x 7.90 x 2.29 cm)	3.56 x 3.11 x 0.98" (9.04 x 7.90 x 2.29 cm)
Weight	0.8 oz (22.68 g)	0.7 oz (19.86 g)	1.0 oz (28.35 g)	3.6 oz (101 g)	3.6 oz (101 g)
Material	Aluminum Housing	Aluminum Housing	Aluminum Housing	DIN Rail Housing	DIN Rail Housing
Available Sensor	Standard, LED or EMI	Standard, LED or EMI	EMI Only	Used with Standard or LED Sensor	Used with EMI Sensor Only
UV Bands/ Power Source	UVA/UVB/UVC or UVV L365/L385/ L395 or L405	UVA/UVB/UVC or UVV L365/L385/ L395 or L405	UVA/UVB/UVC or UVV	20-28 Volts AC or DC 70 mA maximum	20-28 Volts AC or DC 70 mA maximum
Operating Range (Temp °C)	UVA, UVB, UVV: 0-100°C UVC & L-Bands: 0-70°C	UVA, UVB, UVV: 0-100°C UVC & L-Bands: 0-70°C	UVA, UVB, UVV: 0-100°C UVC: 0-70°C	0-50°C	0-50°C
Sensor Aperture/ Output	Sensors are available in multiple aperture sizes, specified at time of order Aperture size used dependent on lamp power & mounting location			0-10 VDC or 4-20 milli- Amp proportional to UV intensity	0-10 VDC or 4-20 milli- Amp proportional to UV intensity
Cable Type	Standard or LED Sensor: 2 wire, Teflon shielded, 10' (3 m) standard EMI Sensor: 3 wire twisted, Teflon shielded, 10' (3 m) standard			At DIN: Two Wire	At DIN: Two Wire + EMI Sensor Grounded
Acceptance Angle / Accuracy	Approximate acceptance angle of 5° degrees	Approximate acceptance angle of 13° degrees	Approximate acceptance angle of 4° degrees	+/- 3% of full scale (10 Volts), Alarm Set Points +/- 5% from threshold setting	+/- 3% of full scale (10 Volts), Alarm Set Points +/- 5% from threshold setting

<u>EIT Quartz Rod</u>


Some UV applications/sources have limited physical space and/or high temperatures which make it difficult to find a suitable location to install the Compact Sensor. The EIT Quartz Rod solves this challenge and allows the user to track the UV conditions while keeping the Compact Sensor cool. The EIT Quartz Rod is made of high quality quartz and is four inches (10 cm) long with a diffuse outer surface. The 0.2" (0.5 cm) diameter of the Quartz Rod allows it to fit into CS-1 housing with a set screw.



Top Left: Compact Sensor with Quartz Rod installed

Bottom Left: Quartz Rod illuminated with UV

Right: Close up of set screw holding the Quartz Rod into a CS-1 Sensor housing




CABLING

A Compact Sensor is connected to the DIN Rail with a supplied 10 foot (3 meter) Teflon shielded cable. *Standard & LED* Compact Sensors utilize a two-wire cable while *EMI* Compact Sensors utilize a three-wire cable. The cable from the Compact Sensor carries a low signal level and should be kept as short as possible and away from high voltage power lines. Longer cable runs should be done after the DIN Rail Signal Conditioning.

Contact EIT to discuss stock/custom cable lengths and/or bulkhead connector options.

MERCURY COMPACT SENSOR RESPONSE


The Compact Sensor response for **mercury** sources is specified at the time of order from the choices below: UVA (320-390 nm) UVB (280-320 nm) UVC* (240-260 nm) UVV (395-445 nm)



EIT Mercury (Broadband) Responses: UVC, UVB, UVA, UVV *The Compact Sensor UVC Response is 240-260 nm

LED COMPACT SENSOR RESPONSE

The Compact Sensor response for LED sources is



EIT L-395 Response shown as an example

<u>Авоит EIT2.0 LLC</u>

EIT2.0 LLC was formed in 2022 under the same ownership and key management team to focus and accelerate the development of EIT's proprietary UV measurement products. Originally established in 1977, EIT has provided engineering & contract electronic manufacturing services (EMS) for medical, industrial, analytical instrument, telecommunications and aerospace customers. EIT's UV measurement products which include radiometers and on-line measurement systems have been sold worldwide since 1986. Over 100,000 EIT products have been sold to measure LED, broadband and UV germicidal sources.

For more information contact EIT or one of our authorized representatives or distributors

EIT Products are designed and manufactured in the USA Product Specifications Subject to Change without Notice

ONLINE SAL-B1006 Rev 01.01 March 2023

UV@EIT20.COM · WWW.EIT20.COM · (571) 578-3075 • 900 SYCOLIN ROAD S SUITE 130 LEESBURG, VA 20175